

Quadri*Sil Horizontal Line Post
Insulator

By OHIO BRASS
Catalog # [P300025S0070](#)



3" Line Post, Standard Leak, Two Hole Blade, Steel Gain Base
with 12" and 14" CL holes for 1" bolts.

*Representative Image

Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	7500 LB
Cantilever Bending Strength - Routine	3750 LB
Catalog Number	P300025S0070
Fitting - Ground End	Steel Gain
Fitting - Live Line End	Tear Drop Blade
Number of Sheds	21
Shed Style	Uniform
UPC	096359699040

Dimensions

Angle	14
Diameter - Shed(s)	8.2

Length	17 in
Length - Effective	38.5 in
Rod Diameter	3 in
Width	8.07 in

Electrical Ratings

Arc Distance - Dry	27.8 (708MM)
Creep and Leakage Distance	82 (2083MM)
Critical Impulse Flashover (CIFO) - Negative	515
Critical Impulse Flashover (CIFO) - Positive	400
Flashover Voltage - 60 Hz Dry	275
Flashover Voltage - 60 Hz Wet	240
Voltage Rating	69 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[Specifications - P300025S0070](#)