

HUBBELL

Power Systems

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P300025S1040](#)



3" Line Post, Standard Leak, Horizontal Clamptop, Steel Flat Base with 8"x10" holes for 3/4" bolts, 9"x13" holes for 7/8" bolts, and 14" CL holes for 1" bolts.

*Representative Image

Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	5000 LB
Cantilever Bending Strength - Routine	2500 LB
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Horizontal Clamp Top
Number of Sheds	21
Shed Style	Uniform

Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	17 in
Length - Effective	39.4 in
Rod Diameter	3 in
Width	10 in

Electrical Ratings

Arc Distance - Dry	27.8 (708MM)
Creep and Leakage Distance	82 (2083MM)
Critical Impulse Flashover (CIFO) - Negative	515
Critical Impulse Flashover (CIFO) - Positive	400
Flashover Voltage - 60 Hz Dry	275
Flashover Voltage - 60 Hz Wet	240
Voltage Rating	69 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)



A Hubbell brand