

## Quadri\*Sil Horizontal Line Post Insulator

By OHIO BRASS  
Catalog # [P300026S1130](#)



3" Line Post, Standard Leak, Horizontal Clamptop, Steel Flat Base with 8"x10" holes for 3/4" bolts, 9"x13" holes for 7/8" bolts, and 14" CL holes for 1" bolts.

\*Representative Image

### Features

- Made from hydrophobic silicone polymer

### General

Cantilever Bending Strength - Max.	5000 LB
Cantilever Bending Strength - Routine	2500 LB
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Horizontal Clamp Top
Number of Sheds	22
Shed Style	Uniform

### Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	12 in
Length - Effective	40.6 in
Rod Diameter	3.000 in
Width	9 in

### Electrical Ratings

Arc Distance - Dry	29.2 (741MM)
Creep and Leakage Distance	85.7 (2176MM)
Critical Impulse Flashover (CIFO) - Negative	535
Critical Impulse Flashover (CIFO) - Positive	440
Flashover Voltage - 60 Hz Dry	285
Flashover Voltage - 60 Hz Wet	255
Voltage Rating	69 kV

### Product Assets

[Catalogs - Quadri\\*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)

[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)

[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)

[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)