

HUBBELL

Power Systems

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P300052S1070](#)

3" Line Post, Standard Leak, Horizontal Clamptop, Steel Gain Base with 12" and 14" CL holes for 1" bolts.



Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	4740 LB
Cantilever Bending Strength - Routine	2370 LB
Fitting - Ground End	Steel Gain
Fitting - Live Line End	Horizontal Clamp Top
Number of Sheds	43
Shed Style	Uniform

Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	17 in
Length - Effective	65.3 in
Rod Diameter	3 in
Width	8.07 in

Electrical Ratings

Arc Distance - Dry	54.5 (1384MM)
Creep and Leakage Distance	163.9 (4163MM)
Critical Impulse Flashover (CIFO) - Negative	935
Critical Impulse Flashover (CIFO) - Positive	835
Flashover Voltage - 60 Hz Dry	535
Flashover Voltage - 60 Hz Wet	485
Voltage Rating	161 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)