

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # P300057S0080



*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	4440 LB
Cantilever Bending Strength - Routine	2220 LB
EU RoHS Indicator	Contact Manufacturer
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Tear Drop Blade
Number of Sheds	47
Shed Style	Uniform
UPC	096359575528

Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	15 in
Length - Effective	69.1 in
Rod Diameter	3.000 in
Width	10 in

Electrical Ratings

Arc Distance - Dry	59.4 (1511MM)
Creep and Leakage Distance	178.9 (4544MM)
Critical Impulse Flashover (CIFO) - Negative	1010
Critical Impulse Flashover (CIFO) - Positive	915
Flashover Voltage - 60 Hz Dry	585
Flashover Voltage - 60 Hz Wet	530
Voltage Rating	161 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)

[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)

[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)

[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)