

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P300063S1130](#)



3" Line Post, Standard Leak, Horizontal Clamptop, Steel Flat Base with 8"x10" holes for 3/4" bolts, 9"x13" holes for 7/8" bolts, and 14" CL holes for 1" bolts.

*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	3990 LB
Cantilever Bending Strength - Routine	1995 LB
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Horizontal Clamp Top
Number of Sheds	52
Shed Style	Uniform

Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	12 in
Length - Effective	75.9 in
Rod Diameter	3.000 in
Width	9 in

Electrical Ratings

Arc Distance - Dry	65.4 (1666MM)
Creep and Leakage Distance	197.5 (5016MM)
Critical Impulse Flashover (CIFO) - Negative	1105
Critical Impulse Flashover (CIFO) - Positive	1005
Flashover Voltage - 60 Hz Dry	645
Flashover Voltage - 60 Hz Wet	585
Voltage Rating	161 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)

[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)

[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)

[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)