

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # P300064S1040



3" Line Post, Standard Leak, Horizontal Clamp Top, Steel Flat Base with 8"x10" holes for 3/4" bolts, 9"x13" holes for 7/8" bolts, and 14" CL holes for 1" bolts.

*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	3920 LB
Cantilever Bending Strength - Routine	1960 LB
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Horizontal Clamp Top
Number of Sheds	53
Shed Style	Uniform

Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	17 in
Length - Effective	77.1 in
Rod Diameter	3.000 in
Width	10 in

Electrical Ratings

Arc Distance - Dry	66.7 (1697MM)
Creep and Leakage Distance	201 (5110MM)
Critical Impulse Flashover (CIFO) - Negative	1125
Critical Impulse Flashover (CIFO) - Positive	1025
Flashover Voltage - 60 Hz Dry	655
Flashover Voltage - 60 Hz Wet	600
Voltage Rating	161 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)

[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)

[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)

[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)