

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P300074S1130](#)



*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	3440 LB
Cantilever Bending Strength - Routine	1720 LB
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Horizontal Clamp Top
Number of Sheds	61
Shed Style	Uniform

Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	12 in
Length - Effective	86.5 in
Rod Diameter	3.000 in
Width	9 in

Electrical Ratings

Arc Distance - Dry	76.4 (1943MM)
Creep and Leakage Distance	231 (5867MM)
Critical Impulse Flashover (CIFO) - Negative	1275
Critical Impulse Flashover (CIFO) - Positive	1175
Flashover Voltage - 60 Hz Dry	750
Flashover Voltage - 60 Hz Wet	690
Voltage Rating	230 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)

[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)

[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)

[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)