

HUBBELL

Power Systems

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P300105S0080](#)



3" Line Post, Standard Leak, Two Hole Blade, Steel Flat Base with 8"x10" holes for 3/4" bolts, 9"x13" holes for 7/8" bolts, and 14" CL holes for 1" bolts.

*Representative Image

Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	2480 LB
Cantilever Bending Strength - Routine	1240 LB
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Tear Drop Blade
Number of Sheds	87
Shed Style	Uniform

Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	15 in
Length - Effective	116.2 in
Rod Diameter	3 in
Width	10 in

Electrical Ratings

Arc Distance - Dry	107.9 (2740MM)
Creep and Leakage Distance	328 (8329MM)
Critical Impulse Flashover (CIFO) - Negative	1765
Critical Impulse Flashover (CIFO) - Positive	1665
Flashover Voltage - 60 Hz Dry	1060
Flashover Voltage - 60 Hz Wet	975
Voltage Rating	345 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)



A Hubbell brand