


Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P350057S0070](#)



3.5" Line Post, Standard Leak, Two Hole Blade, Steel Gain Base with 14" CL holes for 1" bolts.

*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	6080 LB
Cantilever Bending Strength - Routine	3040 LB
Fitting - Ground End	Steel Gain
Fitting - Live Line End	Tear Drop Blade
Number of Sheds	24
Shed Style	Uniform
UPC	096359611622

Dimensions

Angle	15
Diameter - Shed(s)	8.2
Length	18 in
Length - Effective	71.1 in
Rod Diameter	3.500 in
Width	14 in

Electrical Ratings

Arc Distance - Dry	58.3 (1481)
Creep and Leakage Distance	151 (3835)
Critical Impulse Flashover (CIFO) - Negative	995
Critical Impulse Flashover (CIFO) - Positive	900
Flashover Voltage - 60 Hz Dry	575
Flashover Voltage - 60 Hz Wet	525
Voltage Rating	161 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)

[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)

[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)

[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)