

HUBBELL Power Systems

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P350066S0030](#)



3.5" Line Post, Standard Leak, Two Hole Blade, Steel Flat Base
with 14" CL holes for 1-1/4" bolts, and 10"x15" holes for 7/8" bolts.

*Representative Image

Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	5530 LB
Cantilever Bending Strength - Routine	2765 LB
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Tear Drop Blade
Number of Sheds	28
Shed Style	Uniform

Dimensions

Angle	15
Diameter - Shed(s)	8.2
Length	18 in
Length - Effective	80.4 in
Rod Diameter	3.5 in
Width	12 in

Electrical Ratings

Arc Distance - Dry	67.8 (1722)
Creep and Leakage Distance	176.5 (4483)
Critical Impulse Flashover (CIFO) - Negative	1145
Critical Impulse Flashover (CIFO) - Positive	1045
Flashover Voltage - 60 Hz Dry	670
Flashover Voltage - 60 Hz Wet	610
Voltage Rating	161 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)



A Hubbell brand