

HUBBELL Power Systems

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P350099S0070](#)

3.5" Line Post, Standard Leak, Two Hole Blade, Steel Gain Base
with 14" CL holes for 1" bolts.



Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	3660 LB
Cantilever Bending Strength - Routine	1830 LB
Fitting - Ground End	Steel Gain
Fitting - Live Line End	Tear Drop Blade
Number of Sheds	42
Shed Style	Uniform

Dimensions

Angle	15
Diameter - Shed(s)	8.2
Length	18 in
Length - Effective	112.5 in
Rod Diameter	3.5 in
Width	14 in

Electrical Ratings

Arc Distance - Dry	101 (2565)
Creep and Leakage Distance	264 (6705)
Critical Impulse Flashover (CIFO) - Negative	1660
Critical Impulse Flashover (CIFO) - Positive	1565
Flashover Voltage - 60 Hz Dry	995
Flashover Voltage - 60 Hz Wet	915
Voltage Rating	230 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)