

## Glass Bell Suspension w/ Zinc Sleeve, 25000 lb

By OHIO BRASS  
Catalog # [PCN12146DC](#)

5-3/4" x 10" Glass Bell Suspension w/ Zinc Sleeve.



\*Representative Image

### Features

- Toughened glass insulator
- Full range of ANSI or CSA class insulators

### Application

Glass Bell Suspension

### General

Break Strength	45 N·m (400 lb·in)
Fitting - Ground/Base	CS-5 Socket
Fitting - Live Line End	CS-5 Ball
Material	Glass
Material - End Fitting	Galvanized Steel w/ Zinc Sleeve
Strength Rating - Ultimate	25000 lb

### Dimensions

Diameter - Bell	255 mm (10")
Height	5.75 in
Weight	8.6 lb

### Electrical Ratings

Creep and Leakage Distance	320 mm (12-5/8")
Critical Impulse Flashover (CIFO) - Negative	130 kV
Critical Impulse Flashover (CIFO) - Positive	125 kV
Flashover Voltage - 60 Hz Dry	80 kV
Flashover Voltage - 60 Hz Wet	50 kV

### Certifications and Compliance

Industry Standard(s)	CSA
----------------------	-----

### Logistics

Pallet Quantity	90
Standard Package	6

### Product Assets

[Catalogs - Toughened Glass Insulators Catalog \(CA8051E\)](#)  
[Video - Ohio Brass SGD Glass Insulator \(VI0840E\)](#)