

Glass Bell Suspension, 30000 lb

By OHIO BRASS
Catalog # [PCN14146](#)



5-3/4" x 10" Glass Bell Suspension w/ Zinc Sleeve.

Features

- Toughened glass insulator
- Full range of ANSI or CSA class insulators

Application

Glass Bell Suspension

General

Break Strength	45 N-m (400 lb-in)
Catalog Number	PCN14146
Fitting - Ground/Base	52-5-H Socket
Fitting - Live Line End	52-5-H Ball
Material	Glass
Material - End Fitting	Galvanized Steel
Strength Rating - Ultimate	30000 lb
UPC	096359807445

Dimensions

Diameter - Bell	255 mm (10")
Height	5.75 in
Weight	9 lb

Electrical Ratings

Creep and Leakage Distance	320 mm (12-5/8")
Critical Impulse Flashover (CIFO) - Negative	130 kV
Critical Impulse Flashover (CIFO) - Positive	125 kV
Flashover Voltage - 60 Hz Dry	80 kV
Flashover Voltage - 60 Hz Wet	50 kV

Certifications And Compliance

Industry Standard(s)	ANSI
----------------------	------

Logistics

Pallet Quantity	90
Standard Package	6

Product Assets

- [Catalogs - Toughened Glass Insulators Catalog](#)
- [Literature - Silicone Insulators](#)
- [Sales Drawings - Glass Insulator CS-5 \(Reference Only\)](#)
- [Specifications - PCN14146](#)
- [Video - Ohio Brass SGD Glass Insulator](#)