

Glass Bell Suspension, 36000 lb CSA

By OHIO BRASS
Catalog # [PCN160146](#)

5-3/4" x 11" Glass Bell Suspension.



*Representative Image

Features

- Toughened glass insulator
- Full range of ANSI or CSA class insulators

Application

Glass Bell Suspension

General

| | |
|----------------------------|--------------------|
| Break Strength | 45 N·m (400 lb·in) |
| Fitting - Ground/Base | CS-8 Socket |
| Fitting - Live Line End | CS-8 Ball |
| Material | Glass |
| Material - End Fitting | Galvanized Steel |
| Strength Rating - Ultimate | 36000 lb |

Dimensions

| | |
|-----------------|--------------|
| Diameter - Bell | 280 mm (11") |
| Height | 5.75 in |
| Weight | 14.1 lb |

Electrical Ratings

| | |
|----------------------------------------------|--------------|
| Creep and Leakage Distance | 380 mm (15") |
| Critical Impulse Flashover (CIFO) - Negative | 130 kV |
| Critical Impulse Flashover (CIFO) - Positive | 125 kV |
| Flashover Voltage - 60 Hz Dry | 80 kV |
| Flashover Voltage - 60 Hz Wet | 50 kV |

Certifications and Compliance

| | |
|----------------------|-----|
| Industry Standard(s) | CSA |
|----------------------|-----|

Logistics

| | |
|------------------|---|
| Pallet Quantity | 1 |
| Standard Package | 6 |

Product Assets

[Catalogs - Toughened Glass Insulators Catalog \(CA8051E\)](#)
[Sales Drawings - Glass Insulator CS-8 \(PCN160146\) \(Reference Only\)](#)
[Video - Ohio Brass SGD Glass Insulator \(VI0840E\)](#)