

**Glass Bell Suspension, 40000 lb
CSA**

By OHIO BRASS
Catalog # [PCN180146](#)



5-3/4" x 11" Glass Bell Suspension.

Features

- Toughened glass insulator
- Full range of ANSI or CSA class insulators

Application

Glass Bell Suspension

General

Break Strength	48 N-m (400 lb-in)
Catalog Number	PCN180146
Fitting - Ground/Base	CS-8 Socket
Fitting - Live Line End	CS-8 Ball
Material	Glass
Material - End Fitting	Galvanized Steel
Strength Rating - Ultimate	40000 lb
UPC	096359807575

Dimensions

Diameter - Bell	280 mm (11")
Height	5.75 in
Weight	14.1 lb

Electrical Ratings

Creep and Leakage Distance	380 mm (15")
Critical Impulse Flashover (CIFO) - Negative	130 kV
Critical Impulse Flashover (CIFO) - Positive	125 kV
Flashover Voltage - 60 Hz Dry	80 kV
Flashover Voltage - 60 Hz Wet	50 kV

Certifications And Compliance

Industry Standard(s)	CSA
----------------------	-----

Logistics

Pallet Quantity	90
Standard Package	6

Product Assets

[Catalogs - Toughened Glass Insulators Catalog](#)
[Literature - Silicone Insulators](#)
[Specifications - PCN180146](#)
[Video - Ohio Brass SGD Glass Insulator](#)