

HUBBELL

Power Systems

Glass Bell Suspension, 50000 lb CSA

By OHIO BRASS
Catalog # [PCN21156](#)

6-1/8" x 11" Glass Bell Suspension.



Features

- Toughened glass insulator
- Full range of ANSI or CSA class insulators

General

Application	Glass Bell Suspension
Break Strength	45 N·m (400 lb·in)
Fitting - Ground/Base	CS-11 Socket
Fitting - Live Line End	CS-11 Ball
Material	Glass
Material - End Fitting	Galvanized Steel
Strength Rating - Ultimate	50000 lb

Dimensions

Diameter - Bell	280 mm (11")
Height	6.12 in
Weight	16.5 lb

Electrical Ratings

Creep and Leakage Distance	380 mm (15")
Critical Impulse Flashover (CIFO) - Negative	140 kV
Critical Impulse Flashover (CIFO) - Positive	140 kV
Flashover Voltage - 60 Hz Dry	80 kV
Flashover Voltage - 60 Hz Wet	50 kV

Certifications And Compliance

Industry Standard(s)	CSA
----------------------	-----

Logistics

Pallet Quantity	1
Standard Package	6

Product Assets

[Catalogs - Toughened Glass Insulators Catalog](#)
[Sales Drawings - Glass Insulator CS-11 \(Reference Only\)](#)



A Hubbell brand