

PH3 Arrester (240 kV Rated, 7990 mm Creep Distance, AA Hardware)

By OHIO BRASS
Catalog # [PH3300GH240AA](#)

IEC Station Medium / Polymer Housed Surge Arrester

Features

- IEC silicone Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

| | |
|----------------|--------------------------|
| Catalog Number | PH3300GH240AA |
| Color | Gray Housing |
| Material | Silicone Polymer Housing |
| Type | Station |

Electrical Ratings



| | |
|---|----------|
| Frequency Rating | 48-62 Hz |
| Pressure Relief Capability-Symmetrical rms (kA) | 63 |

Certifications And Compliance

| | |
|----------------------|-----|
| Industry Standard(s) | IEC |
|----------------------|-----|

Product Assets

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Specifications - PH3300GH240AA](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)