

PH4 Arrester (30 kV Rated, 2130 mm Creep Distance, AA Hardware)

By OHIO BRASS
Catalog # [PH4036GV030AA](#)

IEC Station High / Polymer Housed Surge Arrester

Features

- IEC silicone Station High class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Catalog Number	PH4036GV030AA
Color	Gray Housing
Material	Silicone Polymer Housing
Type	Station

Electrical Ratings



Frequency Rating	48-62 Hz
Pressure Relief Capability-Symmetrical rms (kA)	63

Certifications And Compliance

Industry Standard(s)	IEC
----------------------	-----

Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Specifications - PH4036GV030AA](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)