

HUBBELL Power Systems

Quadri*Sil Suspension Insulator

By OHIO BRASS
Catalog # [S025029E2010](#)

25kip Extra High Leak, Eye Eye



Features

Made from hydrophobic silicone polymer

General

Application	Suspension
Fitting - Ground End	Y-Clevis
Fitting - Live Line End	Ball
Material	Silicone Rubber
Material - End Fitting	Steel
Number of Sheds	26
Shed Style	Alternating
Tensile Strength	25 kip 5/8 IN (16 MM)
Tensile Strength - Routine	12,500 lbs

Dimensions

Diameter - Shed(s)	Major: 5.83", Minor: 4.61"
Length - Effective	41.3 in
Rod Diameter	0.625 in
Thickness - Housing	> 3MM
Weight	13.4 lb

Electrical Ratings

Arc Distance - Dry	31.6 IN (802.6 MM)
Creep and Leakage Distance	124 IN (3149.6 MM)
Critical Impulse Flashover (CIFO) - Negative	505 kV
Critical Impulse Flashover (CIFO) - Positive	520 kV
Flashover Voltage - 60 Hz Dry	315 kV
Flashover Voltage - 60 Hz Wet	295 kV
Voltage Rating	69/115 kV
kV Class	110 kV

Certifications And Compliance

Industry Standard(s) [ANSI](#)

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Sales Drawings - S025029E2010](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-S025029E2010-SPEC-EN | REV 6/2024