

Quadri*Sil Suspension Insulator

By OHIO BRASS
Catalog # S025032S0000

25kip Standard leak, Eye Eye



*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Fitting - Ground End	Chain Eye
Fitting - Live Line End	Chain Eye
Material	Silicone Rubber
Material - End Fitting	Ductile Iron
Number of Sheds	30
Shed Style	Uniform
Strength Rating - Ultimate	25000 lb
Tensile Strength	25 kip, 5/8" (16 mm)
Tensile Strength - Routine	12,500 lbs
UPC	096359608110

Dimensions

Diameter - Shed(s)	2.9 IN
Length - Effective	45.74 in
Rod Diameter	0.625 in
Thickness - Housing	> 3MM

Electrical Ratings

Arc Distance - Dry	32.3 IN (821 MM)
Creep and Leakage Distance	83 IN (2096 MM)
Critical Impulse Flashover (CIFO) - Negative	460 kV
Critical Impulse Flashover (CIFO) - Positive	475 kV
Flashover Voltage - 60 Hz Dry	340 kV
Flashover Voltage - 60 Hz Wet	320 kV
Withstand Voltage - 60 Hz Wet	205 kV
Withstand Voltage - Lightning Impulse (Negative)	545 kV
Withstand Voltage - Lightning Impulse (Positive)	560 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)
[Test Documents - Prototype Test Report - Quadri*Sil Suspension Insulators - 5/8" Rod \(R17-09-01\)](#)