

Quadri*Sil Suspension Insulator

By OHIO BRASS
Catalog # [S025036S2000](#)

25kip Standard leak, Y Eye



*Representative Image

Features

- Made from hydrophobic silicone polymer

General

EU RoHS Indicator	Contact Manufacturer
Fitting - Ground End	Y-Clevis
Fitting - Live Line End	Chain Eye
Material	Silicone Rubber
Material - End Fitting	Ductile Iron
Number of Sheds	34
Shed Style	Uniform
Strength Rating - Ultimate	25000 lb
Tensile Strength	25 kip, 5/8" (16 mm)
Tensile Strength - Routine	12,500 lbs
UPC	096359443261

Dimensions

Diameter - Shed(s)	2.9 IN
Length - Effective	50.04 in
Rod Diameter	0.625 in
Thickness - Housing	> 3MM

Electrical Ratings

Arc Distance - Dry	36.6 IN (931 MM)
Creep and Leakage Distance	94 IN (2375 MM)
Critical Impulse Flashover (CIFO) - Negative	525 kV
Critical Impulse Flashover (CIFO) - Positive	540 kV
Flashover Voltage - 60 Hz Dry	385 kV
Flashover Voltage - 60 Hz Wet	365 kV
Withstand Voltage - 60 Hz Wet	230 kV
Withstand Voltage - Lightning Impulse (Negative)	620 kV
Withstand Voltage - Lightning Impulse (Positive)	635 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)
[Test Documents - Prototype Test Report - Quadri*Sil Suspension Insulators - 5/8" Rod \(R17-09-01\)](#)