

Quadri*Sil Suspension Insulator

By OHIO BRASS
Catalog # [S025052E2010](#)

25kip Extra High Leak, Eye Eye



Features

- Made from hydrophobic silicone polymer

Application

Suspension

General

Fitting - Ground End	Y-Clevis
Fitting - Live Line End	Ball
Material	Silicone Rubber
Material - End Fitting	Steel
Number of Sheds	46
Shed Style	Alternating
Tensile Strength	25 kip 5/8 IN (16 MM)
Tensile Strength - Routine	12,500 lbs

Dimensions

Diameter - Shed(s)	Major: 5.83", Minor: 4.61"
Length - Effective	64.1 in
Rod Diameter	0.625 in
Thickness - Housing	> 3MM
Weight	20.5 lb

Electrical Ratings

Arc Distance - Dry	54.4 IN (1381.8 MM)
Creep and Leakage Distance	221 IN (5613.4 MM)
Critical Impulse Flashover (CIFO) - Negative	880 kV
Critical Impulse Flashover (CIFO) - Positive	860 kV
Flashover Voltage - 60 Hz Dry	535 kV
Flashover Voltage - 60 Hz Wet	500 kV
Voltage Rating	138/161 kV
kV Class	161 kV

Certifications and Compliance

Industry Standard(s)	ANSI
----------------------	------

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc. Sales Drawings - S025052E2010](#)