

Horseshoe Fiber Drop Storage,
Strand Mount

By Opti-Loop
Catalog # [DCSU8TMK](#)

OptiLoop 8" Horseshoe Fiber Drop Storage, Strand Mount.

Features

- 25% calcium carbonate filled impact copolymer polypropylene construction
- Aluminum Bracket and Bugnut with Galvanized Nut and Bolt
- Stainless Steel Mounting Hardware

Application

Strand/Messenger Cable storage

General

Cable Tie Notch	Yes
Catalog Number	DCSU8TMK
Material	25% calcium carbonate filled impact copolymer polypropylene
Material - Bolt	Galvanized steel
Material - Hex Nut	Galvanized
Product Category	Communications Connectors
UPC	096359642572
Wraps	Multiple

Dimensions

Diameter - Inside	7 in
Diameter - Outside	8 in
Dimensions	8.200 in x 8.400 in x 5.000 in
Height	5 in
Length	8.2 in



Weight	0.471 lb
Width	8.4 in

Conductor Related

Conductor Diameter - Maximum	0.313 in
Conductor Diameter - Minimum	0.25 in
Conductor Diameter Range	0.25 - 0.313
Conductor Type	Messenger Strand
Messenger Diameter - Maximum	0.25 in
Messenger Diameter - Minimum	0.313 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	-----------------------------------------------------

Logistics

Pallet Quantity	320
-----------------	-----

Product Assets

- [Catalogs - Opti-Loop Storage Systems](#)
- [Installation Manuals - Opti-Loop™ Horse Shoe Installation](#)
- [Literature - Opti-Loop Horse-shoe](#)
- [Sales Drawings - CC-23321](#)
- [Specifications - DCSU8TMK](#)
- [Video - Hubbell Power Systems In Depth: Opti-loop Horseshoe](#)