

Strand Mount Aerial Slack Storage System, 24" Dia.

By OPTILOOP
Catalog # FOS24TMK

OptiLoop 24.125" Strand Mount Aerial Slack Storage System, 6005 Alloy Aluminum, Dual coat baked on polyester powder coat



*Representative Image

Features

- 6005 alloy aluminum construction with continuous welds at cross bars and ends
- Dual coat baked on polyester powder coat finish
- Tie eyelets accommodate both stainless steel and plastic ties.
- Radius ends ensure no sharp corners.
- The outward-facing channel design and minimal surface area minimizes stress and ice loading.
- Aluminum brackets and bugnuts with galvanized nuts and bolts

Application

Strand/Messenger Cable storage

General

Cable Tie Eyelet	Yes
Finish Type	Dual Coat Baked On Polyester Powder Coat
Material	6005 Alloy Aluminum
Product Category	Communications Connectors
UPC	096359706977
Wraps	Single

Dimensions

Diameter - Inside	24.125 in
Diameter - Outside	25.4 in
Dimensions	35.378 in x 25.877 in x 3.726 in
Height	3.726 in
Length	35.378 in
Weight	7.100 lb
Width	25.877 in

Conductor Related

Conductor Type	Messenger Strand
Messenger Diameter - Maximum	0.25 in
Messenger Diameter - Minimum	0.313 in

Logistics

Pallet Quantity	42
-----------------	----

Product Assets

[Catalogs - Opti-Loop Storage Systems \(CA05037E\)](#)
[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Opti-Loop FOS \(SF05021E\)](#)
[Sales Drawings - CC-21800](#)
[Video - Opti-Loop® Lashed Aerial Installation \(VI0590E\)](#)