

Strand Mount Aerial Slack Storage System, 12" Dia. Multi-wrap

By OPTILOOP
Catalog # FOS2TMK

OptiLoop 12.125" Strand Mount Aerial Slack Storage System, 6005 Alloy Aluminum, Dual coat baked on polyester powder coat



*Representative Image

Features

- 6005 alloy aluminum construction with continuous welds at cross bars and ends
- Dual coat baked on polyester powder coat finish
- Tie eyelets accommodate both stainless steel and plastic ties.
- Radius ends ensure no sharp corners.
- The outward-facing channel design and minimal surface area minimizes stress and ice loading.
- Aluminum brackets and bugnuts with galvanized nuts and bolts

Application

Strand/Messenger Cable storage

General

Cable Tie Eyelet	Yes
Finish Type	Dual Coat Baked On Polyester Powder Coat
Material	6005 Alloy Aluminum
Product Category	Communications Connectors
UPC	096359706984
Wraps	Multi

Dimensions

Diameter - Inside	12.125 in
Diameter - Outside	13.4 in
Dimensions	25.940 in x 14.377 in x 3.726 in
Height	3.726 in
Length	25.940 in
Weight	4.400 lb
Width	14.377 in

Conductor Related

Conductor Type	Messenger Strand
Messenger Diameter - Maximum	0.25 in
Messenger Diameter - Minimum	0.313 in

Logistics

Pallet Quantity	120
-----------------	-----

Product Assets

[Catalogs - Opti-Loop Storage Systems \(CA05037E\)](#)

[Catalogs - Distribution Connectors \(CA05127E\)](#)

[Literature - Opti-Loop FOS \(SF05021E\)](#)

[Sales Drawings - CC-21800](#)

[Video - Hubbell Power Systems In Depth: Opti-loop Plastic vs Aluminum \(VI05100E\)](#)

[Video - Opti-Loop® Lashed Aerial Installation \(VI0590E\)](#)