

Strand Mount Aerial Slack Storage
System, 18" Dia.

By Opti-Loop
Catalog # [FOS4TMK](#)

OptiLoop 18.125" Strand Mount Aerial Slack Storage System,
6005 Alloy Aluminum, Dual coat baked on polyester powder
coat

Features

- 6005 alloy aluminum construction with continuous welds at cross bars and ends
- Dual coat baked on polyester powder coat finish
- Tie eyelets accommodate both stainless steel and plastic ties.
- Radius ends ensure no sharp corners.
- The outward-facing channel design and minimal surface area minimizes stress and ice loading.
- Aluminum brackets and bugnuts with galvanized nuts and bolts

Application

Strand/Messenger Cable storage

General

Cable Tie Eyelet	Yes
Catalog Number	FOS4TMK
Finish Type	Dual Coat Baked On Polyester Powder Coat
Material	6005 Alloy Aluminum
Product Category	Communications Connectors
UPC	096359707011
Wraps	Single

Dimensions

Diameter - Inside	18.125 in
Diameter - Outside	19.7 in



*Representative Image

Dimensions	31.688 in x 20.500 in x 2.813 in
Height	2.813 in
Length	31.688 in
Weight	6.1 lb
Width	20.5 in

Conductor Related

Conductor Type	Messenger Strand
Messenger Diameter - Maximum	0.25 in
Messenger Diameter - Minimum	0.313 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	75
-----------------	----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Catalogs - Opti-Loop Storage Systems](#)
- [Literature - Opti-Loop FOS](#)
- [Sales Drawings - CC-21800](#)
- [Specifications - FOS4TMK](#)
- [Video - Hubbell Power Systems In Depth: Opti-loop Plastic vs Aluminum](#)
- [Video - Opti-Loop® Lashed Aerial Installation](#)