

Strand Mount Aerial Slack Storage
System, 17" Dia. Plastic

By Opti-Loop
Catalog # [FOSP17TMKBABA](#)

OptiLoop 17.50" Strand Mount Aerial Slack Storage System, 25% calcium carbonate filled impact copolymer polypropylene

Features

- 25% calcium carbonate filled impact copolymer polypropylene construction
- Aluminum brackets and bugnuts with galvanized nuts and bolts
- Stainless steel mounting hardware

Application

Strand/Messenger Cable storage

General

Catalog Number	FOSP17TMKBABA
Material	25% calcium carbonate filled impact copolymer polypropylene

Dimensions

Diameter - Inside	17.5 in
Diameter - Outside	18.8 in
Dimensions	25.083 in x 19.495 in x 3.008 in
Height	3.008 in
Length	25.083 in
Weight	5.4 lb
Width	19.495 in



Conductor Related

Conductor Diameter - Maximum	0.313 in
Conductor Diameter - Minimum	0.25 in
Conductor Diameter Range	0.25 - 0.313
Conductor Type	Messenger Strand
Messenger Diameter - Maximum	0.25 in
Messenger Diameter - Minimum	0.313 in

Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2025)
--------------------------	--

Logistics

Pallet Quantity	96
-----------------	----

Product Assets

- [Catalogs - Opti-Loop Storage Systems](#)
- [Sales Drawings - CC-21802](#)
- [Specifications - FOSP17TMK](#)
- [Video - Hubbell Power Systems In Depth: Opti-loop Plastic vs Aluminum](#)
- [Video - Opti-Loop® Lashed Aerial Installation](#)