



PBSS1

by Wiegmann
Catalog ID: PBSS1

N4X 30.5 MM 1 Pushbutton Enclosure 3.5X3.2X2.8 304 Stainless Steel

- Bodies and doors fabricated from 14 gauge 304 stainless steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Grounding provisions provided.

Product Details

General

Application	Designed to hold all standard brands of pushbuttons, switches, and pilot lights. Provide protection from dust, dirt, oil, and water. PBSS Series designed for areas where serious corrosion problems exist.
Construction	Continuously Welded Seams
Cover Type	Pushbutton
Knockouts	No
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Holes	1
Pushbutton Number of Holes	1
Pushbutton Size	30.5 MM
Series	PBSS
Type	Enclosure
UPC	786725433056

Dimensions

Actual Depth	2.81 in
Actual Height	3.500 in
Actual Width	3.250 in
Depth	3 in

Height	4 in
Weight	1.67 lb
Width	3 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	4X
UL Listed	Yes