



## PBSS3A

by Wiegmann  
Catalog ID: PBSS3A

N4X 30.5 MM 3 Pushbutton Enclosure 8X3.2X2.8 316 Stainless Steel

- Bodies and doors fabricated from 14 gauge 316 stainless steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Grounding provisions provided.

## Product Details

### General

Application	Designed to hold all standard brands of pushbuttons, switches, and pilot lights. Provide protection from dust, dirt, oil, and water. PBSS Series designed for areas where serious corrosion problems exist.
Construction	Continuously Welded Seams
Cover Type	Pushbutton
Knockouts	No
Listings	UL, CSA
Material	316 Stainless Steel
Mounting Type	Wall Mount
Number of Holes	3
Pushbutton Number of Holes	3
Pushbutton Size	30.5 MM
Series	PBSS-A
Type	Enclosure
UPC	786725845637

### Dimensions

Actual Depth	2.81 in
Actual Width	3.250 in
Depth	3 in
Height	8 in

Weight	3 lb
Width	3 in

## Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	4X
UL Listed	Yes