

by Wiegmann Catalog ID: PBXD16SS

N4X 30.5 MM 16 Deep Pushbutton Enclosure 11.7X10.7X4.8 304 Stainless Steel

 Bodies and doors fabricated from 14 gauge 304 stainless steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Enclosures have internal detachable hinges to hold cover open during wiring, yet permit quick removal. Grounding provisions provided.

Product Details

General

Application	Designed to hold 30.5mm oil-tight pushbuttons, switches, and pilot lights. Provide protection against dirt, dust, oil, and water. Extra deep design accommodates additional contact blocks for pushbuttons.
Construction	Continuously Welded Seams
Cover Type	Pushbutton
Knockouts	No
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Holes	16
Pushbutton Number of Holes	16
Pushbutton Size	30.5 MM
Series	PBXD-SS
Туре	Enclosure
UPC	786725845675

Dimensions

Actual Depth	4.810 in
Actual Height	11.750 in
Actual Length	4.81 in

Actual Width	10.750 in	
Depth	5 in	
Height	12 in	
Weight	12 lb	
Width	11 in	
Certifications and Compliance		
Certified Listed	• UL • CSA	
Nema Rating	4X	
UL Listed	Yes	