

Porcelain Test Terminal - 2000A

By PCORE Electric
Catalog # [B-63056-E-70](#)

Porcelain Test Terminal - 2000A (345kV)



*Representative Image

Features

- No need to remove overhead cables / bus work
- Speeds up the testing process
- Saves money due to reduced labor

General

| | |
|-----------------------|---|
| Bottom Terminal Type | 1 1/2"-12 Female Thread |
| Color | Gray |
| Material | Copper - Silver Plated |
| Material - Insulation | Porcelain |
| Top Terminal Type | 4-Hole NEMA Pad @ 1.75" Spacing with (1) Corona Ring |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 20.50 in x 13.88 in x 20.50 in |
| Height | 20.50 in |
| Length | 20.50 in |
| Weight | 71 lb |
| Width | 13.88 in |

Electrical Ratings

| | |
|----------------|--------|
| Current Rating | 2000 A |
| kV Class | 345 kV |

Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services \(CA02038E\)](#)
[Installation Manuals - Instructions for Installation and Use of PCORE® Test Terminals \(B-30756 Rev 01-16-19\)](#)
[Sales Drawings - Test Terminal With One Corona Ring On Top Terminal \(63056-E_and_70\)](#)
[Video - PCORE Electric Bushings Test Terminal \(VI02005E\)](#)