

Porcelain Test Terminal - 4000A

By PCORE Electric
Catalog # [B-63070-46-EE-70](#)

Porcelain Test Terminal - 4000A (500kV & 765kV)



*Representative Image

Features

- No need to remove overhead cables / bus work
- Speeds up the testing process
- Saves money due to reduced labor

General

Bottom Terminal Type	4-Hole NEMA Pad @ 1.75" Spacing with (1) Corona Ring
Color	Gray
Material	Copper - Silver Plated
Material - Insulation	Porcelain
Top Terminal Type	6-Hole NEMA Pad in Horizontal Position @ 1.75" Spacing with (1) Corona Ring

Dimensions

Length 28.25 in

Electrical Ratings

Current Rating 4000 A
kV Class 500 kV;765 kV

Product Assets

[Installation Manuals - Instructions for Installation and Use of PCORE® Test Terminals \(B-30756 Rev 01-16-19\)](#)
[Sales Drawings - Test Terminal Two Corona Rings- Top & Bottom Terminals \(63070-46-EE_and_70\)](#)
[Video - PCORE Electric Bushings Test Terminal \(VI02005E\)](#)