

## Porcelain Test Terminal - 3000A

By PCORE Electric  
Catalog # [B-63071-70](#)

Porcelain Test Terminal - 3000A (230kV and below)



### Features

- No need to remove overhead cables / bus work
- Speeds up the testing process
- Saves money due to reduced labor

### General

Bottom Terminal Type	3"-12 Female Thread
Color	Gray
Material	Copper - Silver Plated
Material - Insulation	Porcelain
Top Terminal Type	4-Hole NEMA Pad @ 1.75" Spacing

### Dimensions

Dimensions	20.00 in x 8.31 in x 20.00 in
Height	20.00 in
Length	20.00 in
Weight	70 lb
Width	8.31 in

### Electrical Ratings

Current Rating	3000 A
kV Class	230 kV

### Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services \(CA02038E\)](#)  
[Installation Manuals - Instructions for Installation and Use of PCORE® Test Terminals \(B-30756 Rev 01-16-19\)](#)  
[Sales Drawings - Test Terminal \(63071\\_and\\_70\)](#)  
[Video - PCORE Electric Bushings Test Terminal \(VI02005E\)](#)