

Porcelain Test Terminal - 4000A

By PCORE Electric
Catalog # [B-63080-25-70](#)

Porcelain Test Terminal - 4000A (230kV and below)



*Representative Image

Features

- No need to remove overhead cables / bus work
- Speeds up the testing process
- Saves money due to reduced labor

General

Bottom Terminal Type	4"-10 Female Thread
Color	Gray
Material	Copper - Silver Plated
Material - Insulation	Porcelain
Top Terminal Type	4-Hole NEMA Pad @ 1.75" Spacing

Dimensions

Length	25.00 in
--------	----------

Electrical Ratings

Current Rating	4000 A
kV Class	230 kV

Product Assets

[Installation Manuals - Instructions for Installation and Use of PCORE® Test Terminals \(B-30756 Rev 01-16-19\)](#)
[Sales Drawings - Test Terminal \(63080-25_and_70\)](#)
[Video - PCORE Electric Bushings Test Terminal \(VI02005E\)](#)