

## Porcelain Test Terminal - 4000A

By PCORE Electric  
Catalog # [B-64008-22-41-EE-70](#)

Porcelain Test Terminal - 4000A (500kV & 765kV)



\*Representative Image

### Features

- No need to remove overhead cables / bus work
- Speeds up the testing process
- Saves money due to reduced labor

### General

Bottom Terminal Type	4"-12 Female Thread with (1) Corona Ring
Color	Gray
Material	Copper - Silver Plated
Material - Insulation	Porcelain
Top Terminal Type	6-Hole NEMA Pad in Horizontal Position @ 1.75" Spacing with (1) Corona Ring

### Dimensions

Length 25.00 in

### Electrical Ratings

Current Rating 4000 A  
kV Class 500 kV;765 kV

### Product Assets

[Installation Manuals - Instructions for Installation and Use of PCORE® Test Terminals \(B-30756 Rev 01-16-19\)](#)  
[Video - PCORE Electric Bushings Test Terminal \(VI02005E\)](#)