

Porcelain Test Terminal - 1600A

By PCORE Electric
Catalog # [B-63040-E-70](#)

Porcelain Test Terminal - 1600A (345kV)



*Representative Image

Features

- No need to remove overhead cables / bus work
- Speeds up the testing process
- Saves money due to reduced labor

General

Bottom Terminal Type	1 1/4"-12 Female Thread
Color	Gray
Material	Copper - Silver Plated
Material - Insulation	Porcelain
Top Terminal Type	4-Hole NEMA Pad @ 1.75" Spacing with (1) Corona Ring

Dimensions

Length	20.5 in
--------	---------

Electrical Ratings

Current Rating	1600 A
kV Class	345 kV

Product Assets

[Installation Manuals - Instructions for Installation and Use of PCORE® Test Terminals](#)
[Video - PCORE Electric Bushings Test Terminal](#)