

## Porcelain Test Terminal - 2000A

By PCORE Electric  
Catalog # [B-63056-E-70](#)

Porcelain Test Terminal - 2000A (345kV)



\*Representative Image

### Features

- No need to remove overhead cables / bus work
- Speeds up the testing process
- Saves money due to reduced labor

### General

Bottom Terminal Type	1 1/2"-12 Female Thread
Color	Gray
Material	Copper - Silver Plated
Material - Insulation	Porcelain
Top Terminal Type	4-Hole NEMA Pad @ 1.75" Spacing with (1) Corona Ring

### Dimensions

Dimensions	20.50 in x 13.88 in x 20.50 in
Height	20.5 in
Length	20.5 in
Weight	71 lb
Width	13.88 in

### Electrical Ratings

Current Rating	2000 A
kV Class	345 kV

### Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instructions for Installation and Use of PCORE® Test Terminals](#)
- [Sales Drawings - Test Terminal With One Corona Ring On Top Terminal](#)
- [Video - PCORE Electric Bushings Test Terminal](#)