

Porcelain Test Terminal - 4000A

By PCORE Electric  
Catalog # [B-63070-25-70](#)

Porcelain Test Terminal - 4000A (230kV and below)



\*Representative Image

Features

- No need to remove overhead cables / bus work
- Speeds up the testing process
- Saves money due to reduced labor

General

Bottom Terminal Type	4-Hole NEMA Pad @ 1.75" Spacing
Catalog Number	B-63070-25-70
Color	Gray
Material	Copper - Silver Plated
Material - Insulation	Porcelain
Top Terminal Type	4-Hole NEMA Pad @ 1.75" Spacing

Dimensions

Dimensions	28.25 in x 10.56 in x 28.25 in
------------	--------------------------------

Height	28.25 in
Length	28.25 in
Weight	155 lb
Width	10.56 in

Electrical Ratings

Current Rating	4000 A
kV Class	230 kV

Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instructions for Installation and Use of PCORE® Test Terminals](#)
- [Sales Drawings - Test Terminal](#)
- [Specifications - B630702570](#)
- [Video - PCORE Electric Bushings Test Terminal](#)