

## Porcelain Test Terminal - 4000A

By PCORE Electric  
Catalog # [B-63070-25-EE-70](#)

Porcelain Test Terminal - 4000A (500kV & 765kV)



\*Representative Image

### Features

- No need to remove overhead cables / bus work
- Speeds up the testing process
- Saves money due to reduced labor

### General

Bottom Terminal Type	4-Hole NEMA Pad @ 1.75" Spacing with (1) Corona Ring
Color	Gray
Material	Copper - Silver Plated
Material - Insulation	Porcelain
Top Terminal Type	4-Hole NEMA Pad @ 1.75" Spacing with (1) Corona Ring

### Dimensions

Length	28.25 in
--------	----------

### Electrical Ratings

Current Rating	4000 A
kV Class	500 kV;765 kV

### Product Assets

- [Installation Manuals - Instructions for Installation and Use of PCORE® Test Terminals](#)
- [Sales Drawings - Test Terminal Two Corona Rings- Top & Bottom Terminals](#)
- [Video - PCORE Electric Bushings Test Terminal](#)