

Porcelain Test Terminal - 3000A

By PCORE Electric
Catalog # [B-63071-70](#)



Porcelain Test Terminal - 3000A (230kV and below)

Features

- No need to remove overhead cables / bus work
- Speeds up the testing process
- Saves money due to reduced labor

General

| | |
|-----------------------|------------------------------------|
| Bottom Terminal Type | 3"-12 Female Thread |
| Color | Gray |
| Material | Copper - Silver Plated |
| Material - Insulation | Porcelain |
| Top Terminal Type | 4-Hole NEMA Pad @ 1.75" Spacing |

Dimensions

| | |
|------------|-------------------------------|
| Dimensions | 20.00 in x 8.31 in x 20.00 in |
| Height | 20 in |
| Length | 20 in |
| Weight | 70 lb |
| Width | 8.31 in |

Electrical Ratings

| | |
|----------------|--------|
| Current Rating | 3000 A |
| kV Class | 230 kV |

Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
[Installation Manuals - Instructions for Installation and Use of PCORE® Test Terminals](#)
[Sales Drawings - Test Terminal](#)
[Video - PCORE Electric Bushings Test Terminal](#)