

POC type bushing - 69KV

By PCORE Electric
Catalog # [B-88013-306-70](#)

POC® 69KV-400/1200A Transformer-Circuit Breaker Bushing, Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Draw lead Connected for Air-to-Oil Applications , 21.00" Min. Oil Immersion Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog Number B-88013-306-70
Type Condenser Bushings

Dimensions

Dimensions 72.56 in x 11 in x 72.56 in
Height 72.56 in
Length 72.56 in
Minimum Oil Level 21



*Representative Image

Weight 155 lb
Width 11 in

Electrical Ratings

BIL 350 kV
Current Rating 400/1200 A
kV Class 69 kV

Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instruction Manual for POC® Bushings](#)
- [Sales Drawings - 88013-306-70](#)
- [Specifications - B8801330670](#)