

POC type bushing - 69KV

By PCORE Electric
Catalog # [B-88023-335-70](#)

POC® 69KV-2000A Transformer-Circuit Breaker Bushing, Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Draw lead Connected for Air-to-Oil Applications , 17.69" Min. Oil Immersion Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog Number	B-88023-335-70
Type	Condenser Bushings

Dimensions

Dimensions	70.19 in x 15.25 in x 70.19 in
Height	70.19 in
Length	70.19 in
Minimum Oil Level	17.69



*Representative Image

Weight	200 lb
Width	15.25 in

Electrical Ratings

BIL	350 kV
Current Rating	2000 A
kV Class	69 kV

Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instruction Manual for POC® Bushings](#)
- [Sales Drawings - 88023-335-70](#)
- [Specifications - B8802333570](#)