

POC type bushing - 25KV

By PCORE Electric
Catalog # [B-88743-174-70](#)

POC® 25KV-4000A Transformer-Circuit Breaker Bushing,
Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Draw lead
Connected for Air-to-Oil Applications , 21.00" Min. Oil Immersion
Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog Number B-88743-174-70
Type Condenser Bushings

Dimensions

Dimensions 52.25 in x 11 in x 52.25 in
Height 52.25 in
Length 52.25 in
Minimum Oil Level 21



*Representative Image

Weight 141 lb
Width 11 in

Electrical Ratings

BIL 150 kV
Current Rating 4000 A
kV Class 25 kV

Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instruction Manual for POC® Bushings](#)
- [Sales Drawings - 88743-174-70](#)
- [Specifications - B8874317470](#)