

POC type bushing - 25KV

By PCORE Electric
Catalog # [B-88753-358-70](#)

POC® 25KV-5000A Transformer-Circuit Breaker Bushing, Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Draw lead Connected for Air-to-Oil Applications , 21.00" Min. Oil Immersion Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog Number	B-88753-358-70
Type	Condenser Bushings

Dimensions

Dimensions	53.13 in x 13.25 in x 53.13 in
Height	53.13 in
Length	53.13 in
Minimum Oil Level	21



*Representative Image

Weight	230 lb
Width	13.25 in

Electrical Ratings

BIL	150 kV
Current Rating	5000 A
kV Class	25 kV

Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instruction Manual for POC® Bushings](#)
- [Sales Drawings - 88753-358-70](#)
- [Specifications - B8875335870](#)