

POC type bushing - 25KV

By PCORE Electric
Catalog # [B-88772-269-70](#)

POC® 25KV-7000A Transformer-Circuit Breaker Bushing, Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Draw lead Connected for Air-to-Oil Applications , 16.50" Min. Oil Immersion Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog Number	B-88772-269-70
Type	Condenser Bushings

Dimensions

Dimensions	55.25 in x 17 in x 55.25 in
Height	55.25 in
Length	55.25 in



*Representative Image

Minimum Oil Level	16.5
Weight	300 lb
Width	17 in

Electrical Ratings

BIL	150 kV
Current Rating	7000 A
kV Class	25 kV

Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
[Installation Manuals - Instruction Manual for POC® Bushings](#)
[Specifications - B8877226970](#)