

POC type bushing - 34.5KV

By PCORE Electric
Catalog # [B-88832-334-70](#)

POC® 34.5KV-3000A Transformer-Circuit Breaker Bushing,
Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Draw lead
Connected for Air-to-Oil Applications , 16.50" Min. Oil Immersion
Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog Number B-88832-334-70
Type Condenser Bushings

Dimensions

Dimensions 52 in x 11.5 in x 52 in
Height 52 in
Length 52 in
Minimum Oil Level 16.5



*Representative Image

Weight 145 lb
Width 11.5 in

Electrical Ratings

BIL 200 kV
Current Rating 3000 A
kV Class 34.5 kV

Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instruction Manual for POC® Bushings](#)
- [Sales Drawings - 88832-334-70](#)
- [Specifications - B8883233470](#)