

POC type bushing - 34.5KV

By PCORE Electric  
Catalog # [B-88833-144-70](#)

POC® 34.5KV-3000A Transformer-Circuit Breaker Bushing,  
Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Draw lead  
Connected for Air-to-Oil Applications , 21.00" Min. Oil Immersion  
Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog NumberB-88833-144-70  
TypeCondenser Bushings

Dimensions

Dimensions55.94 in x 10 in x 55.94 in  
Height55.94 in  
Length55.94 in  
Minimum Oil Level21



\*Representative Image

Weight135 lb  
Width10 in

Electrical Ratings

BIL200 kV  
Current Rating3000 A  
kV Class34.5 kV

Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test  
Terminals and Services](#)
- [Installation Manuals - Instruction Manual for POC® Bushings](#)
- [Sales Drawings - 88833-144-70](#)
- [Specifications - B8883314470](#)