

POC type bushing - 34.5KV

By PCORE Electric
Catalog # [B-88843-291-70](#)

POC® 34.5KV-4000A Transformer-Circuit Breaker Bushing,
Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Draw lead
Connected for Air-to-Oil Applications , 21.00" Min. Oil Immersion
Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog Number B-88843-291-70
Type Condenser Bushings

Dimensions

Dimensions 57.51 in x 11 in x 57.51 in
Height 57.51 in
Length 57.51 in



*Representative Image

Minimum Oil Level 21
Weight 170 lb
Width 11 in

Electrical Ratings

BIL 200 kV
Current Rating 4000 A
kV Class 34.5 kV

Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test
Terminals and Services](#)
[Installation Manuals - Instruction Manual for POC® Bushings](#)
[Specifications - B8884329170](#)