

POC type bushing - 34.5KV

By PCORE Electric
Catalog # [B-88843-9-70](#)

POC® 34.5KV-4000A Transformer-Circuit Breaker Bushing, Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Draw lead Connected for Air-to-Oil Applications , 21.00” Min. Oil Immersion Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog Number	B-88843-9-70
Type	Condenser Bushings

Dimensions

Dimensions	60 in x 11 in x 60 in
Height	60 in
Length	60 in
Minimum Oil Level	21



*Representative Image

Weight	175 lb
Width	11 in

Electrical Ratings

BIL	200 kV
Current Rating	4000 A
kV Class	34.5 kV

Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instruction Manual for POC® Bushings](#)
- [Sales Drawings - 88843-9-70](#)
- [Specifications - B88843970](#)